





**3517**

<b>CAT. NO. 3517</b>	
<b>FUSE SIZE</b>	<b>L DIM.</b>
5mm x 20mm	.910 (23.1)



**FIGURE 1**

Mounting Detail




**3517**




**3518P**

<b>CAT. NO. 3518P</b>	
<b>FUSE SIZE</b>	<b>L DIM.</b>
5mm x 20mm	.910 (23.1)



**FIGURE 2**

Mounting Detail




**3518P**




**3512**

<b>CAT. NO. 3512</b>	
<b>FUSE SIZE</b>	<b>L DIM.</b>
5mm x 20mm	.910 (23.1)



**FIGURE 3**

Mounting Detail




**3512**




**3512P**

<b>CAT. NO. 3512P</b>	
<b>FUSE SIZE</b>	<b>L DIM.</b>
5mm x 20mm	.910 (23.1)



**FIGURE 4**

Mounting Detail




**3512P**




**3520**

<b>CAT. NO. 3520</b>	
<b>FUSE SIZE</b>	<b>L DIM.</b>
5mm x 20mm	.900 (22.9)



**FIGURE 5**

Mounting Detail



**3520**



3519

CAT. NO. 3519	
FUSE SIZE	L DIM.
5mm × 20mm	.650 (16.5)





FIGURE 6

Mounting Detail



3519



3521

CAT. NO. 3521	
FUSE SIZE	L DIM.
2AG	.514 (13.1)
5mm × 20mm	.710 (18.1)





FIGURE 7

Mounting Detail



3521




3561

CAT. NO. 3561	
FUSE SIZE	L DIM.
2AG	.354 (9.0)
5mm × 20mm	.500 (12.7)



FIGURE 8

Pad Layout




3561




3562

CAT. NO. 3562	
FUSE SIZE	L DIM.
5mm × 20mm	.820 (20.9)
3AG	




3AG



5mm

FIGURE 9

Mounting Detail




3562

NOTE: ALL MOUNTING DIMENSIONS ARE FOR REFERENCE ONLY. PLEASE VERIFY YOUR FUSE LAYOUT PRIOR TO FABRICATION.


**FIGURE 10**



3565



Mounting Detail



3565


**CAT. NO. 3565**

DESIGNATION	FUSE SIZE	L DIM.
4AG	.281 (7.1) × 1.250 (31.8)	1.000 (25.4)


**FIGURE 11**



3566



Mounting Detail



3566


**CAT. NO. 3566**

DESIGNATION	FUSE SIZE	L DIM.
BBS	.406 (10.3) × 1.375 (34.9)	1.515 (38.5)
5AG	.406 (10.3) × 1.500 (38.1)	1.640 (41.7)


**FIGURE 12**



3529



Mounting Detail



3514


**CAT. NO. 3510, 3511, 3513, 3514, 3529**

DESIGNATION	FUSE SIZE	L DIM.
1AG	.250 (6.4) × .625 (15.9)	.750 (19.1)
7AG	.250 (6.4) × .875 (22.2)	1.000 (25.4)
8AG	.250 (6.4) × 1.000 (25.4)	1.125 (28.6)
3AG	.250 (6.4) × 1.250 (31.8)	1.375 (34.9)


**FIGURE 13**



3516P



Mounting Detail



3515

**CAT. NO. 3515, 3515P, 3516P**

DESIGNATION	FUSE SIZE	L DIM.
1AG	.250 (6.4) × .625 (15.9)	.735 (18.7)
7AG	.250 (6.4) × .875 (22.2)	.985 (25.0)
8AG	.250 (6.4) × 1.000 (25.4)	1.100 (28.0)
3AG	.250 (6.4) × 1.250 (31.8)	1.360 (34.6)


ORIENTATION LEGS	
CAT. NO.	W
3515	.062 (1.57)
3515P	.095 (2.4)
3516P	.122 (3.1)

**FIGURE 14**

FOR THRU HOLE MOUNT APPLICATIONS



3530




3530

**FOR CAT. NO. 3530**

DESIGNATION	FUSE SIZE	L DIM.
1AG	.250 (6.4) × .625 (15.9)	.450 (11.4)
7AG	.250 (6.4) × .875 (22.2)	.700 (17.8)
8AG	.250 (6.4) × 1.000 (25.4)	.825 (21.0)
3AG	.250 (6.4) × 1.250 (31.8)	1.075 (27.3)

Mounting Detail




**FIGURE 15**

FOR RIVET MOUNT APPLICATIONS



3570




3535

**FOR CAT. NO. 3531, 3533, 3535, 3570, 4246, 4247**

DESIGNATION	FUSE SIZE	L DIM.
1AG	.250 (6.4) × .625 (15.9)	.450 (11.4)
7AG	.250 (6.4) × .875 (22.2)	.700 (17.8)
8AG	.250 (6.4) × 1.000 (25.4)	.825 (21.0)
3AG	.250 (6.4) × 1.250 (31.8)	1.075 (27.3)

Mounting Detail




**FIGURE 16**

FOR SURFACE MOUNT APPLICATIONS



4247




3533

**FOR CAT. NO. 3531, 3533, 3535, 3570, 4246, 4247**

DESIGNATION	FUSE SIZE	L DIM.
1AG	.250 (6.4) × .625 (15.9)	.120 (3.0)
7AG	.250 (6.4) × .875 (22.2)	.365 (9.3)
8AG	.250 (6.4) × 1.000 (25.4)	.490 (12.4)
3AG	.250 (6.4) × 1.250 (31.8)	.740 (18.8)

Pad Layout



**FIGURE 17**

FOR SURFACE MOUNT APPLICATIONS



3532



3567

**FOR CAT. NO. 3532, 3567**

DESIGNATION	FUSE SIZE	L DIM.
1AG	.250 (6.4) × .625 (15.9)	.195 (5.0)
7AG	.250 (6.4) × .875 (22.2)	.445 (11.3)
8AG	.250 (6.4) × 1.000 (25.4)	.570 (14.5)
3AG	.250 (6.4) × 1.250 (31.8)	.820 (20.8)

Pad Layout

